

FIXERS

FOR BLACK-AND-WHITE FILMS AND PHOTOPAPERS

FOMAFIX

In general

Liquid concentrate of a rapid fixer featuring high efficiency, strong buffer ability and long-term stability.

Use

The fixer is designed for the manual and automatic processing of all sorts of black-and-white films and papers.

Dilution

Manual processing:

1 part of the concentrate + 5 parts of water

Automatic processing:

1 part of the concentrate + 4 parts of water

Fixing capacity

1 litre of working solution (dilution 1 + 5) is sufficient to fix 17 perforated films (135-36) or rollfilms (120), or a corresponding amount of sheet films (up to 40 sheets 13x18 cm, etc.), or 2 sq. m of photopapers on a baryta paper base (FB) and 4 sq. m of photopapers on a RC base.

Packaging

PE-bottle of 0,5 litre.

PE-canister of 5 litres.

FOMAFIX P

In general

Two-component powder acid fixer.

Use

The fixer is designed for the manual processing of all sorts of black-and-white films and papers.

Preparation of working solution

In 600 ml water of 40 °C, the content of the bigger and then of the smaller bag is dissolved, for the processing of films and papers to be filled up with water to a final volume of 750 ml and 1 litre respectively.

Fixing capacity

The working solution prepared is sufficient to fix 15 perforated films (135-36) or rollfilms (120), a corresponding amount of sheet films (up to 35 sheets 13x18 cm, etc.), or 1.5 sq. m of photopapers on a baryta paper base (FB) and 3 sq. m of photopapers on a RC base.

Packaging

Box with two bags of 195 g total weight for 0,75 l and 1 l of solution.

Box with two bags of 975 g total weight for 3,75 l and 5 l of solution.

Manual processing at 20 °C (minutes)

	FOMAFIX	FOMAFIX P
Fomapan 100 Classic	3	10
Fomapan 200 Creative	3	10
Fomapan 400 Action	3	10
Retropan 320 soft	3	10
Foma Ortho 400	3,5	11
Fomabrom	3	5
Fomabrom Variant	3	5
Fomaspeed	1.5	3
Fomaspeed Variant	1.5	3
Fomatone MG Classic	3	5
Retrobrom	3	5

Information of the ecological disposal, principles of safe use at transport, storage and handling are stated in the safety data sheet of the product.

The product has been produced and marketed in conformity with a quality system according to the international standard ISO 9001.